

LASERLUX MASK

SPECIFICATIONS

 Composition	 Average Thickness	 Carrier	 Certifications
Adhesive Polyester	75-80 microns	Siliconized paper	REACH compliant

FOR USE WITH

- the entire Laserlux range

APPLICATION INSTRUCTIONS

- Remove the protective film
- Apply the application tape to the laser-cut material, either by hand or using a calender, taking care to avoid bubbles forming
- Remove the paper backing from the laser-cut material
- Transfer the design following the instructions in the Laserlux technical data sheet
- Remove the application tape whilst still warm

 **NOTE:** We highly recommend to perform a test before launching a production.

 This document can be subject to variations. Updated versions are available on www.siser.com
For further information, please contact our sales office: info@siser.it



Siser s.r.l.
Viale della Tecnica, 18
36100 Vicenza - Italy

Tel. +39 0444.287960
Fax +39 0444.287959
info@siser.it
www.siser.com

r.e.a. vi 171856 reg.
imp. vi n° 14971 c.s.
€ 103.300 i.v. p.iva
01591490246

